



elesa
Original design ERFW+I



Length l	d ₁ H9 Bore	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	t	Ø Knob
38	B 6	15,5	11	3	21	12,5	41	7	15	12
56	B 8	19	13,5	4	28,5	18,5	51,5	8	20	13
71	B 10	23	16	4	30	18	53	9	25	14,5

Specification 3

Body

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, RAL 9005, matte finish ● SW

Hub bushing

Brass

Revolving knob

Plastic, Polyamide (PA)

- Black, matte finish
- Spindle steel
- Zinc plated, blue passivated

RoHS

The design of the cranked handles GN 670.2 matches the product family Ergostyle®.

Attaching the cranked handle on a shaft using a transverse pin or a set screw is made easier with the semilateral cross bore.

The finger recesses of the rotating cylinder head allows a safe grip and the ergonomic operation of the relatively small cranked handle.

Technical Information

	Page
Product Family Ergostyle®	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order

GN 670.2-38-B6-SW

1	Length l
2	d ₁
3	Color