



**elesa**  
Original design ERF./ ERF.N/ ERF.p.



<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub> Thread	<sup>2</sup> d <sub>2</sub> H9 Bore	<sup>2</sup> s H9 Square	<sup>3</sup> l <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	e	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	t <sub>1</sub> min.	t <sub>2</sub> min.
44	M 5	-	-	-	15,5	-	-	-	19	26,5	19	12	-
44	M 6	B 6	V 5	16	15,5	3	M 4	7	19	26,5	19	12	15
63	M 8	B 8	V 6	25	19	4	M 4	8	24,5	35	26,5	13	20
78	M 10	B 10	V 8	30	23	4	M 5	9	29,5	42	32	17	25
95	M 12	B 12	V 10	50	26,5	5	M 5	10	34	51,5	40	20	30

**Specification**

**Handle body**

- Plastic, Polyamide
- Glass fiber reinforced
- Operating temperature -30 °C to 130 °C
- Black-gray, matte finish

**Insert**

- with threaded bushing / bore H9 / square  
Brass
- with threaded stud  
Steel  
Zinc plated, blue passivated

**Grub screw DIN 916**

Steel, blackened

RoHS

Design and handling of the clamping levers GN 601 comply with the requirements and claims of the Ergostyle® product family.

**see also...**

**GN 604** Adjustable Hand Levers (with Internal Thread) Page QVX / QVX

**Technical Information**

Product Family Ergostyle®	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order (Threaded bushing / Bore /Square)

<sup>1</sup> <sup>2</sup>	1	l <sub>1</sub>
<b>GN 601-44-V5</b>	2	s (d <sub>1</sub> , d <sub>2</sub> )

How to order (Threaded stud)

<sup>1</sup> <sup>2</sup> <sup>3</sup>	1	l <sub>1</sub>
<b>GN 601-63-M8-25</b>	2	d <sub>1</sub>
	3	l <sub>2</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

