




Plunger pin retracted





ELESA original design PMT.200



3 Type

- A** without lock nut
- AK** with lock nut

Assembly instruction



Distance bushing GN 609.5

1 d_1 Pin $_{-0.1}^{-0.15}$ Bore $-0,08$	2 d_2	d_3	$l_1 \approx$	l_2	l_3	l_4	s	A/F_1	A/F_2	max. tightening torque in Nm	Spring load in N \approx	
											initial	end
6	M 12 x 1,5	15,5	51	8	26	26,5	8	14	19	10	9	35
8	M 16 x 1,5	20,5	61	10	30	32,5	10	19	24	18	10	40

Specification

- Guide (Threaded body)
Plastic (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130° C
- black, matte
- Plunger pin
- Steel **ST**
 hardened, blackened
- Stainless Steel AISI 303 **NI**
- Spring
Stainless Steel AISI 302
- Latch
Plastic (Polyamide PA)
- black, matte
- not removable
- Lock nut
Plastic (Polyamide PA)
black, matte
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- **RoHS compliant**



Information

Cam action indexing plungers GN 672 are used in cases where the locking pin must not protrude all the time. By rotating the lock through 180° the locking pin withdraws itself. A groove keeps the plunger in this position.

The cam action indexing plungers with plastic guide are a reasonably priced version.

see also...

- *Mounting blocks GN 612.1* → Page 699
- *Mounting blocks GN 412.1* → Page 698
- *Distance bushings GN 609.5* → Page 694
- *Flat Stainless Steel-Hexagonal nuts GN 909.5* → Page 695

How to order

1	d_1
2	d_2
3	Type
4	Material

GN672-6-M12x1,5-AK-ST