



GN 675



Elastomer coating





ELESA Original design EBK.-SOFT



iF product design award

GN 675.1



1

2

d ₁	d ₂			d ₃	d ₄	h ₁	h ₂ ≈	t	
43	M 6*	M 8	M 10	32,5	20	GN 675 55	GN 675.1 53,5	17,5	18
50	M 8	M 10	M 12	37	25	64	60	20	26

* only available for GN 675

Specification

3

- Technopolymer (Polypropylene PP)
 - coated with a soft elastomer (TPE) 70 Shore A
 - temperature resistant up to 80 °C
 - black-gray, matte, similar RAL 7021
- Softline coating chemically bonded with the plastic body
- Bushing Brass
- Color of the cap (GN 675.1)
 - transparent
 - orange, RAL 2004
 - gray, RAL 7035
 - yellow, RAL 1021
 - blue, RAL 5024
 - red, RAL 3000
- Elastomer characteristics → Page 1483
- Plastic characteristics → Page 1483
- RoHS

- DTR
- DOR
- DGR
- DGB
- DBL
- DRT

Accessory

- Positioning and control symbols GN 517.1

Information

The design of the ball handles GN 675 / GN 675.1 matches the product family of the Ergostyle®. The Softline jacket makes the ball handles particularly ergonomic and safe and easy to handle.

The **soft, slip-proof** contact area improves the contact both in hot (hand sweat) and in dry ambient conditions, in the event of oily surfaces and in very high or very low (freezing) temperatures.

The Softline ball handles are suitable for use both as operating elements and for clamping. The „hard“ plastic core guarantees the perfect anchoring engagement of the threaded bushing, also under heavier loads.

The transparent sight cap at GN 675.1 allows symbols to be placed underneath.

Positioning and control symbols are to be ordered separately.

see also...

- Product family Ergostyle® → Page 17
- Product family Softline → Page 17

How to order (without cap)	1	d ₁
GN 675-50-M10	2	d ₂

How to order (with cap)	1	d ₁
GN 675.1-50-M8-DGR	2	d ₂
	3	Color of the cap