



ELESA Original design EKK-SST-SAN



1

2

d ₁	d ₂	d ₃	h ₁	h ₂	t min.
21	M 5	12,5	18	10,5	10
31	M 8	18,5	27	17	15

Specification

3

- Plastic
Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 130 °C
 - black-gray, RAL 7021, matte
 - white, RAL 9016, matte
- Threaded bushing
Stainless Steel AISI 303
- Plastic characteristics
→ Main Catalogue Page 1483
- Stainless Steel characteristics
→ Main Catalogue Page 1489
- RoHS



Information

Knurled knobs GN 676 are manufactured from an antibacterial plastic.

Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antibacterial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antibacterial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

- Knurled knobs GN 676 (Plastic) → Main Catalogue Page 62
- Knobs GN 676.1 (Steel, blackened) → Main Catalogue Page 64
- Mushroom type knobs GN 76 → Main Catalogue Page 58
- Stainless Steel-Knobs GN 676.5 → Main Catalogue Page 64

How to order

GN 676-31-M8-SGA

1 d₁2 d₂

3 Finish