



2 Type
K Steel, standard spring load

1

$d_1 -0,05$	d_2	d_3	l_1	l_2	l_3	w compression	Spring load in N \approx	
							initial	end
6	2,7	8	20	6	3,2	3,5	10	22
8	3,9	10	24	8	3,2	4,5	30	88
10	5,9	13	30	10	4	5,5	42	110
12	7,9	16	36	12	5	6,5	50	130

Specification

- Housing
Steel
blackened
- Bolt
Steel
blackened, case
- Spring
Stainless Steel AISI 631
- ISO-Fundamental tolerances → Page 1479
- RoHS

Information

GN 614.6 spring plungers are primarily used in toolmaking as spring-loaded stops as well as for pressure and hold-off functions.

Tolerance d_1 H7 is recommended for the mounting hole.

siehe auch...

- Spring plungers GN 611 (with thread) → Page 735

How to order

GN614.6-10-K

1 d_1

2 Type