



elesa
Original design EKK.p



1	2	3				4		
d_1	d_2	Length l			d_3	h_1	h_2	
16	M 3	10	16	-	-	8,5	13	8,5
18	M 4	10	16	-	-	10,5	15,5	10,5
21	M 5	10	16	20	-	12,5	18	10,5
21	M 6	16	20	30	-	12,5	18	10,5
25	M 6	16	20	25	30	14,5	22,5	14
25	M 8	20	25	30	40	14,5	22,5	14
31	M 8	20	25	30	40	18,5	27	17
31	M 10	30	40	-	-	18,5	27	17

Specification

Knob

Plastic, polyamide, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, RAL 7021, matte finish

● SG

Threaded stud

Steel

Zinc plated, blue passivated

RoHS

The design of the GN 676 knurled screws matches the product family Ergostyle®.

These knurled screws are used for manual applications for clamping or pulling. The concave top of the nut is a comfortable rest point for the thumb during a pulling application.

The knurled section makes the knobs easier to install and also allows them to be used as knurled screws.

see also...

	Page
GN 676 Knurled Knobs (Plastic, Internal Thread)	QVX
GN 76 Mushroom Shaped Knobs (Phenolic resin)	QVX

Technical Information

Product Family Ergostyle®	QVX
Plastic Characteristics	QVX

How to order

GN 676-31-M8-20-SG

1	d_1
2	d_2
3	Length l
4	Color