



4 Type

A Front rounded,
long version

1 2 3

b h9	h	Length l																	For shaft-Ø from to	
2	2	6	8	10	12	14	16	18	20	-	-	-	-	-	-	-	-	-	-	6... 8
3	3	6	8	10	12	14	16	18	20	22	25	28	30	32	35	36	-	-	-	8...10
4	4	6	8	10	12	14	16	18	20	22	25	28	32	36	40	45	-	-	-	10...12
5	5	8	10	12	14	16	18	20	22	25	28	32	36	40	45	50	-	-	-	12...17
6	6	12	14	16	18	20	22	25	28	32	36	40	45	50	56	63	-	-	-	17... 22
8	7	12	14	16	18	20	22	25	28	32	36	40	45	50	56	63	70	80	90	22...30
10	8	16	18	20	22	25	28	32	36	40	45	50	56	63	70	80	90	100	110	30...38
12	8	20	25	28	32	36	40	45	50	56	63	70	80	90	100	125	-	-	-	38...44

Specification

- Steel C45 Plain
- ISO Fundamental Tolerances → Page 2151
- RoHS

On request

- b = 14, 16, 18, 20

Information

Parallel keys DIN 6885 are only in packing units of 50 pieces for each size and length available.

see also...

- Keyway Type in the Bore and the Shaft → Page 2078

How to order

1 2 3 4
DIN 6885-6-6-28-A

1	b
2	h
3	Length l
4	Type