



elesa
Original design IZP.

- 3 Type**
- N** neutral
 - M** With arrow
 - S** with scale 0...9, 20 graduations

1 d_1 f7	2 d_2 H8 Bore	d_3	d_4	d_5	d_6	l_1	l_2	l_3	t_1	t_2
27	B 6	22	25	20,5	M 4	30	12	18	24	12
32	B 8	25	30	25	M 4	38	13	23	30	13
35	B 10	28	33	26,5	M 5	45	15	27	37	15
40	B 12	33	38	31	M 5	52	16,5	32	44	16

Specification

- Knob**
 Plastic, Polyamide (PA)
 • Glass fiber reinforced
 • Operating temperature 0 °C to +130 °C
 • Black, shiny finish
 • Arrow for type M
 White, laser-engraved
 • Scale for type S)
 White, laser-engraved
- Cover**
 Aluminum
 Anodized, natural color
- Nut / Grub screw DIN 916**
 Steel
- RoHS

On request

- Special graduations (see „How to Order Graduatiions“)

Besides the standard scale (Type S) the control knobs GN 626 can be supplied with any type of graduation. Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to Order Graduatiions“

see also...	Page
GN 526 Control Knobs (Plastic, with Steel Bushing)	QVX
GN 726 Control Knobs (Aluminium, Black Anodized)	QVX
GN 726.1 Control Knobs (Aluminium, Black Anodized)	QVX

Technical Information

How to order - Graduatiions	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

Accessory

GN 826 Clamping Elements (for Adjustable Spindles)	QVX
---	-----

How to order	
1 d_1	
2 d_2	
3 Type	

GN 626-40-B12-N

