



**2 Type**

- A** Without dowel hole
- B** With dowel hole

**1**

d <sub>1</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub> H11	e	h	k	t
M 5	14	20	1,5	2,5	12	8	7
M 6	16	24	1,5	2,5	14	10	8
M 8	20	30	2	3	17	12	10
M 10	28	36	3	4	20	14	12
M 12	32	40	4	4	24	16	16

**Specification**

- Stainless steel AISI 303 **NI**  
Matte shot-blasted
- *Strength Values of Nuts* → Page 2152
- *ISO Fundamental Tolerances* → Page 2151
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**3**

**Information**

The dowel bore d<sub>5</sub> in the stainless steel knurled nut DIN 6303 is designed for the use of clamping or notch pins.

Knurled nuts DIN 6303 with H7 bore and the size M12 are not provided for on the official standard sheet. In addition, the knurling divisions are larger than the DIN standard for better grip.

see also...

- *Stainless Steel Knurled Nuts GN 536* → Page 640
- *Stainless Steel Knurled Nuts DIN 466* → Page 646

How to order

**DIN 6303-M6-A-NI**

<b>1</b>	d <sub>1</sub>
<b>2</b>	Type
<b>3</b>	Material

