



elesa
Original design I.222

¹ d ₁	² d ₂		d ₃	h	t ₁ min.	t ₂ ±0,5
15	M 6	-	12	25	16	3,5
20	M 8	-	14	31	20	3,5
26	M 8	M 10	17	42	20	5
33	M 10	M 12	20	54	40	8
38	M 12	-	23	68	45	11
41	M 14	M 16	25	87	55	14

Specification

Plastic, phenolic resin (PF)

- Operating temperature -20 °C to +110 °C
- Black, shiny finish

RoHS

Domed gear knobs GN 719 are very often used in place of ball knobs DIN 319 on switch levers, gear levers etc. Knobs for such applications are often chosen for ergonomic reasons.

see also...

	Page
GN 719.1 Domed Gear Knobs (Press-On Type)	QVX
GN 719.2 Domed Gear Knobs (with Thread or Press-On Type)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

GN 719-20-M8

¹ d₁

² d₂