



Type A



Type B



elesa
Original design EWP.



2 Type

- A** Mounting with hex head screw
- B** Mounting with countersunk screw

1

l_1	b_1	b_2	d	h_1	h_2	h_3	h_4	$l_2 \pm 0,5$	l_3	t
114	35	19	6,5	33	7	11	6	93,5	74	5

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +110 °C
- Black-gray, matte finish, similar to RAL 7021

Cover caps

- Plastic, Polyamide (PA)
- Black-gray, RAL 7021, shiny finish
- Orange, RAL 2004, shiny finish
- Gray, RAL 7035, shiny finish
- Yellow, RAL 1021, shiny finish
- Blue, RAL 5024, shiny finish
- Red, RAL 3000, shiny finish
- Green, RAL 6017, shiny finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

The design of the GN 630.1 cabinet U-handles matches the product family of Ergostyle®.

A typical application is on double swing doors on machine shrouds or fixtures.

The cover caps shroud the two mounting screws of the cabinet U-handle. The cover caps are supplied loose.

see also...

	Page
GN 630 Ledge Handles (Polyamid)	QVX
GN 565.2 Inclined Cabinet U-handles (Aluminum, Mounting from the Back or the Operator's Side)	QVX
GN 425.1 Cabinet U-Handles (Steel / Aluminum / Stainless Steel, Angled)	QVX

Technical Information

Product Family Ergostyle®	QVX
Product Family Standard Parts for Profile Systems	QVX
Strength Properties	QVX
Plastic Characteristics	QVX

How to order

GN 630.1-114-A-DOR

1	l_1
2	Type
3	Color of the cover cap