



elesa  
Original design I.222 N

<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b> Bore	<b>d<sub>3</sub></b>	<b>h</b>	<b>t</b>
15	B 6	12	25	17
20	B 8	14	31	21
26	B 10	17	42	30
33	B 10	20	54	37
33	B 12	20	54	40
38	B 14	23	68	50
41	B 16	25	87	58

### Specification

**Plastic**, phenolic resin (PF)

- Operating temperature -20 °C to +110 °C
- Black, shiny finish
- Bushing polyamide, embedded

RoHS

Domed gear knobs GN 719.1 are very often used in place of ball knobs DIN 319 on switch levers, gear levers etc. Domed gear knobs satisfy by their form and ergonomical aspects.

When using these knobs a threaded shaft is not required.

Easy blows with a soft hammer are sufficient to drive the knob into place, the shaft end should be slightly rounded or chamfered (30°).

The Polyamide bushing is embedded during the manufacturing process and it does not need insertion before mounting.

see also...

**GN 719.2** Domed Gear Knobs (with Thread or Press-On Type)

**GN 719** Domed Gear Knobs (with Thread)

Page

QVX

QVX

### Technical Information

ISO Fundamental Tolerances

Plastic Characteristics

QVX

QVX

How to order

**GN 719.1-33-B10**

1 d<sub>1</sub>

2 d<sub>2</sub>