



ROSTFREI®
Inox
Stainless
Steel

² d ₁	³ d ₂	⁴ Length l ≈				d ₄	h ₁	h ₂	h ₃				
32	M 6	16	20	25	30	35	45	-	-	12	20	10	9
40	M 8	16	20	25	30	35	40	45	55	14	25	13	10
50	M 10	25	30	35	45	55	-	-	-	18	32	20	12
63	M 12	30	35	40	50	60	-	-	-	20	40	25	14

Specification

- Knob
Technopolymer (Polyamide PA)
- shock-resistant
- black matte
- **GN 6335.4**
Threaded stud
Steel
zinc plated, blue passivated
- **GN 6335.5**
Threaded stud
Stainless Steel AISI 303
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS



Information

The hand knobs have an immaculate contact or clamping surface thanks to the protruding steel / Stainless Steel bushing.

see also...

- *Hand knobs 6335.4 (without protruding bushing, threaded stud steel)* → Page 423
- *Hand knobs 6335.5 (without protruding bushing, threaded stud Stainless Steel)* → Page 423

How to order (Threaded stud steel)

¹ ² ³ ⁴
GN 6335.4-TE-32-M6-25

¹	Material
²	d₁
³	d₂
⁴	Length l

How to order (Threaded stud Stainless Steel)

¹ ² ³ ⁴
GN 6335.5-TE-63-M12-60

¹	Material
²	d₁
³	d₂
⁴	Length l

