



<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>	<b>l<sub>1</sub></b>			<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>d<sub>5</sub>+0,05</b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>l<sub>4</sub></b>
32	M 6	25	35	45	15	14	4,5	20	10	5,1	3,6	7,6
40	M 8	30	40	50	18	18	6,1	25	13	6,2	4,2	9,2
40	M 8	30	40	50	21	18	6,1	25	13	6,2	5	10
40	M 8	30	40	50	25	18	6,1	25	13	6,2	5,5	10,5
40	M 8	30	40	50	32	18	6,1	25	13	6,2	6	11
40	M 8	30	40	50	40	18	6,1	25	13	6,2	8	13
50	M 10	35	45	55	21	22	7,8	32	17	7,3	4,3	10
50	M 10	35	45	55	25	22	7,8	32	17	7,3	4,6	10,5
50	M 10	35	45	55	32	22	7,8	32	17	7,3	5	11
50	M 10	35	45	55	40	22	7,8	32	17	7,3	7	13

**Specification**

- Star knob DIN 6336  
Plastic  
Technopolymer (Polyamide PA)  
black, matte
- Threaded stud  
Stainless Steel AISI 304 Cu
- Thrust pad  
Plastic  
Technopolymer (Polyacetal POM)  
- temperature resistant up to 80 °C  
- black, matte
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

**Information**

Star knobs GN 6336.11 / GN 6336.12 have a ball pin whose diameter is smaller than the core diameter of the thread.

The movable thrust pad is easily clipped on and taken off.

The thrust pads are supplied disassembled.

see also...

- *Knurled screws GN 421.12 (with movable thrust pad)* → Page 451
- *Star knobs with threaded stud GN 6336.10 with loss protection GN 111.7* → Page 1426

How to order (with ball pin)	1	d <sub>1</sub>
<b>GN 6336.11-40-M8-50</b>	2	d <sub>2</sub>
	3	l <sub>1</sub>

How to order (with movable thrust pad)	1	d <sub>1</sub>
<b>GN 6336.12-50-M10-45-25</b>	2	d <sub>2</sub>
	3	l <sub>1</sub>
	4	d <sub>3</sub>