



ROSTFREI
Inox
Stainless
Steel

3 Type

- A** Latch position right-angled to fixing holes
- B** Latch position parallel to fixing holes

1 d ₁ Pin <small>-0,05 -0,25</small> Bore <small>+0,1 +0,3</small>	2 s	d ₂ +0,2	h	l ₁ ≈	l ₂	l ₃	l ₄	l ₅	m	A/F	t	Spring load in N ≈			
												Steel initial	Steel end	Stainless Steel initial	Stainless Steel end
8	20	6,1	7,5	68	14	35	37	48	34	10	6,1	16	55	16	45
10	20	6,1	7,5	68	14	35	37	48	34	10	6,1	16	55	16	45
12	20	6,1	7,5	68	14	35	37	48	34	10	6,1	16	55	16	45
14	20	6,1	7,5	68	14	35	37	48	34	10	6,1	16	55	16	45

Specification

- Guide
Steel precision cast
- zinc plated, blue passivated
- zinc plated and plastic coated black, textured finish
- Latch
zinc plated, blue passivated
- Plunger pin
Steel, zinc plated, blue passivated
- Spring
Stainless Steel AISI 301
- Guide / Latch
Stainless Steel precision casting weldable, AISI 316
- Plunger pin
Stainless Steel, AISI 316
- Spring
Stainless Steel AISI 316Ti



Information

Spring latches GN 722.2 are used when the plunger pin is temporarily not allowed to protrude. The plunger pin retracts by turning the latch by 180°. A groove will hold the latch in both positions.

ZB

SW

Spring latches GN 722.2 are designed for use in **steel construction** or in **locksmith shops** where less precise positioning / locking is normally required. The dimensional tolerances are therefore chosen to ensure that functional safety is guaranteed under dirt exposure and that cost-effective production methods are used.

see also...

- List of cam action indexing plunger types → Page 701 ff.
- Positioning bushings GN 412.2 → Page 696

A4

- Load rating information → Page 1463
- Stainless Steel characteristics → Page 1489
- RoHS

How to order (Steel)	1 d ₁
	2 s
GN 722.2-12-20-A-SW	3 Type
	4 Color (Finish)

How to order (Stainless Steel)	1 d ₁
	2 s
GN 722.2-10-20-B-A4	3 Type
	4 Material