



1.1

1.2

1.3

1.4

2 3 4

d ₁	d ₂	Length l ≈					d ₄	h ₁	h ₂	h ₃
25	M 5	10	15	20	-	-	10	16	8	6
32	M 6	16	20	25	30	35	12	20	10	8,5
40	M 8	16	20	25	30	35	14	26	13	10
50	M 10	25	30	35	45	55	18	32	17	10
63	M 12	30	35	40	50	60	20	40	21	14

2.1

Specification

- Knob
Technopolymer (Polyamide PA)
- shock-resistant
- black matte

TE

- **GN 6336.4**
Threaded stud
Steel
zinc plated, blue passivated

- **GN 6336.5**
Threaded stud
Stainless Steel AISI 303

• Plastic characteristics → Page 1483

• Stainless Steel characteristics → Page 1489

• RoHS

Information

The star knobs have an immaculate contact or clamping surface thanks to the protruding steel / Stainless Steel bushing.

see also...

- Star knobs 6336.4
(without protruding bushing, threaded stud steel) → Page 399
- Star knobs 6336.5
(without protruding bushing, threaded stud Stainless Steel) → Page 399

2.2

2.3

How to order (Threaded stud steel)

1 2 3 4
GN 6336.4-TE-50-M10-30

1	Material
2	d ₁
3	d ₂
4	Length l

How to order (Threaded stud Stainless Steel)

1 2 3 4
GN 6336.5-TE-40-M8-16

1	Material
2	d ₁
3	d ₂
4	Length l

2.4

