



ELESA Original design M.643/M.643 HT

1 2

Length l	d						a	b	h	t min.				
	Standard material (PP)		HT material (PA)							M4	M5	M6	M8	M10
86 ±0,5	M 5	M 6	-	-	M 6	-	14	23	44	-	10	12	-	-
94 ±0,5	M 5	M 6	-	-	-	-	14	24	48	-	10	12	-	-
117 ±0,5	M 4	M 5	M 6	M 8	M 6	M 8	15	25	49	10	10	12	13	-
120 ±0,5	M 5	M 6	M 8	-	-	-	15	25	49	-	10	12	13	-
132 ±0,5	M 5	M 6	M 8	-	-	-	16	26	54	-	10	12	13	-
150 ±1	M 6	M 8	M 10	-	-	-	16	27	56	-	-	12	13	17
179 ±1	M 8	M 10	-	-	M 8	-	16	27	57	-	-	-	13	17
235 ±1	M 8	M 10	-	-	-	-	18,5	29	61	-	-	-	13	17
300 ±1	M 10	-	-	-	-	-	22	32	64	-	-	-	-	17

Specification

- Plastic Technopolymer (Polypropylene PP)
 - shock-resistant
 - temperature resistant up to 100 °C
 - black, matte finish
- Plastic Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 200 °C
 - black-gray, matte
- Bushing Brass
- *Strength properties* → Page 1449
- *Plastic characteristics* → Page 1483
- RoHS

3

Information

Cabinet U-handles GN 725 are known for their good design and the well proven elliptical profile. They meet the demand from an ergonomic angle.

see also...

- *Cabinet U-handles GN 565 (Aluminum)* → Page 80
- *Cabinet U-handles GN 625 (Plastic)* → Page 89

HT

How to order (resistant up to 100 °C)	1	Length l
GN 725-179-M8	2	d

How to order (resistant up to 200 °C)	1	Length l
GN 725-86-M6-HT	2	d
	3	Material