



3 Type

- N Cover neutral
- M Cover with indicator point

4 Identification no.

- 1 with grub screw
- 2 with collet

1 d_1	2 d_2 H8 Bore		2 d_3 Collet	d_4	d_5	d_6	h_1	h_2	h_3	l	t
22	B 5	-	-	16	14	M 4	15	9	4,3	5	-
27	B 6	-	Z 6	20	18	M 4	17	11	4,3	5,5	14
34	B 6	B 8	Z 8	25	23	M 5	20	14	4,2	7	17
42	B 8	B 10	Z 10	32	30	M 5	23	17	4	8,5	20

Specification

- Aluminum anodized, black
- Cover Plastic, light gray
- Collet / hexagon nut Brass
- Stainless Steel-Grub screw DIN 916 with internal hexagon and serrated point
- ISO-Fundamental tolerances → Page 1479
- RoHS

Information

The light gray cover of the control knobs GN 726 shrouds the fixing components as well as the shaft end. The cover also lends itself for a logo or other symbols.

Made from an aluminum extrusion allows the manufacture of **customized solutions** in existing diameters at relatively low cost.

see also...

- Control knobs GN 726.1 (Aluminum) → Page 260
- Control knobs GN 526 (Plastic) → Page 257
- Clamping elements GN 826 (for adjustment spindles) → Page 268

How to order

GN 726-34-Z8-M-2

1	d_1
2	d_3 (d_2)
3	Type
4	Identification no.

