



d ₁	d ₂	Length l ≈					d ₃	h ₁	h ₂	h ₃
25	M 5	10	15	20	-	-	10	16	8	6
32	M 6	16	20	25	30	35	12	20	10	8,5
40	M 8	16	20	25	30	35	14	26	13	10
50	M 10	25	30	35	45	55	18	32	17	10
63	M 12	30	35	40	50	60	20	40	21	14

Specification

- Knob
Technopolymer (Polyamide PA)
- Shock-resistant
- Black matte finish
- **GN 6336.4**
Threaded stud
Steel
Zinc plated, blue passivated
- **GN 6336.5**
Threaded stud
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS



Information

The star knobs have an immaculate contact or clamping surface thanks to the protruding steel / stainless steel bushing.

see also...

- *Star Knobs 6336.4*
(Plastic, without Protruding Bushing, Threaded Stud Steel) → Page 545
- *Star Knobs 6336.5*
(Plastic, without Protruding Bushing, Threaded Stud Stainless Steel) → Page 547

How to order (Threaded stud steel)

GN 6336.4-TE-50-M10-30

1	Material
2	d ₁
3	d ₂
4	Length l

How to order (Threaded stud stainless steel)

GN 6336.5-TE-40-M8-16

1	Material
2	d ₁
3	d ₂
4	Length l

