



1 2

d <sub>1</sub>	d <sub>2</sub> H8 Bore		b	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	l <sub>1</sub>	l <sub>2</sub>	t <sub>1</sub> min.	t <sub>2</sub> +0,2	s <sup>+0,3 +0,1</sup>
34	B 6	B 8	28	M 5	6	20	20	7,5	14	4	4
42	B 8	B 10	35	M 5	6	30	22	7,5	16	4	4

**Specification**

- Aluminum anodized, black
- Indexing line white, engraved with laser precision
- Stainless Steel-Grub screw DIN 916 with internal hexagon and serrated point
- ISO-Fundamental tolerances → Page 1479
- RoHS

**Information**

Control knobs GN 729 are usually selected for applications which require a limited movement within 180°.

With the aid of limiting pins which protrude into the circular groove the angle of rotation can be restricted. The bore d<sub>4</sub> is for a spring plunger GN 614 to act as a simple detent.

The indexing line is indelible and visible from two sides.

How to order	1	d <sub>1</sub>
	2	d <sub>2</sub>

**GN 729-42-B8**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

