



2 3 4

d ₁	d ₂	Length l ≈																d ₃	h ₁	h ₂		
		Material ST										Material SK										
25	M 5	10	15	20	25	30	-	-	-	-	-	-	10	15	20	25	-	-	-	12	16	8
25	M 6	10	16	20	25	30	35	45	60	-	-	-	-	-	-	-	-	-	-	12	16	8
32	M 6	10	16	20	25	30	35	45	60	-	-	10	16	20	25	30	35	45	14	20	10	
32	M 8	16	20	25	30	35	40	50	55	60	-	-	-	-	-	-	-	-	14	20	10	
40	M 8	16	20	25	30	35	40	50	55	60	-	16	20	25	30	40	55	-	18	25	13	
40	M 10	15	20	25	30	35	40	45	50	55	60	-	-	-	-	-	-	-	18	25	13	
50	M 10	15	20	25	30	35	40	45	50	55	60	25	30	35	45	55	-	-	22	32	17	
50	M 12	20	25	30	35	40	50	60	-	-	-	-	-	-	-	-	-	-	22	32	17	
63	M 12	20	25	30	35	40	50	60	-	-	-	30	35	40	50	60	-	-	26	40	21	
80	M 16	-	-	-	-	-	-	-	-	-	-	30	40	50	60	70	-	-	35	50	25	

Specification

- Knob
Technopolymer (Polyamide PA)
Shock-resistant, black matte finish **ST**
- Knob
Duroplast (PF)
Black shiny finish **SK**
- Threaded stud
Steel
Zinc plated, blue passivated
- Plastic Characteristics → Page 2158
- RoHS

1

Information

- Star knobs GN 6336.4 comply with DIN 6336 type L.
- see also...
- Star Knobs GN 6336.10 (with Brass / Plastic Pivot) → Page 548
 - Star Knobs GN 6336.12 (with Movable Thrust Pad) → Page 549
 - Star Knobs GN 6336.13 (with Loss Protection) → Page 551
 - Star Knobs GN 6336.4 with Loss Protection GN 111.7 → Page QVX

How to order

1	Material
2	d ₁
3	d ₂
4	Length l

GN 6336.4-SK-32-M6-25

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

