



- 4 Type
- M Straight lever
- N Angled lever

1	2	3													
d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>						d <sub>3</sub>		h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub> ≈	l <sub>2</sub>	l <sub>3</sub> ≈	
20	M 8	20	25	32	40	50	63	13,5	20	25	8	46	74	70	
25	M 10	20	25	32	40	50	63	16	25	29	8	58	93	87	
28	M 12	25	32	40	50	63	80	19	30	33,5	10,5	70,5	116	109	

Specification

Hub/Shaft

Steel, blackened

Insert

Steel, blackened

Property class 5.8

Ball knobs DIN 319

Plastic, phenolic resin (PF)

Black, shiny finish

RoHS

Adjustable clamping levers GN 6337.3 have proved to be ideal whenever parts have to be clamped in a confined space or a particular lever position is required. The insert is connected by the lever via serrations in the ball bore which can be disengaged.

Pushing the lever down, disengages the serrations and the lever can be swivelled to the ideal clamping position. Engagement is achieved by releasing the lever.

Should a rotation of 360° not be possible, the insert can be lightly screwed in (after the lever is disengaged) via a slot in the knurled screw.

Technical Information	Page
Strength Values of Screws	QVX
Plastic Characteristics	QVX

How to order	1	d <sub>1</sub>
	2	d <sub>2</sub>
	3	l <sub>1</sub>
	4	Type
GN 6337.3-28-M12-50-N		