


EDELSTAHL®
Rostfrei
Inox
Stainless
Steel

Application example



d₁	d₂	l₁ ^{+0,20 -0,13}		d₃	l₂	l₃	s
M 5	6 ^{-0,03 -0,05}	5	6	7	8	-	-
M 6	8 ^{-0,05 -0,08}	5	6	8	9	10	12
M 8	10 ^{-0,05 -0,08}	8	10	12	14	15	-
M 10	12 ^{-0,05 -0,08}	12	14	16	17	-	-
M 12	14 ^{-0,05 -0,08}	14	16	18	-	-	-
M 14	16 ^{-0,05 -0,08}	17	18	-	-	-	-

Specification

- Steel **ST**
 - Property class 5.8
 - Blackened
 - Case-hardened (all round depth 0.2 to 0.4 mm)
- Stainless steel AISI 303 **NI**
- *Strength Values of Screws* → Page 2152
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

The dimensions d_2 / l_1 of the cylinder head shoulder bolts GN 732.1 permit a use as bearing pin for swing bolts DIN 444, swing bolts GN 1524, swing nuts GN 444.2 and hubs with eccentric cam GN 919.

see also...

- *Swing Bolts DIN 444* → Page 1046
- *Swing Bolts GN 1524 (with Long Threaded Bolt)* → Page 1047
- *Swing Nuts GN 444.2* → Page 1079
- *Hubs with Eccentric Cam GN 919* → Page 674
- *Shoulder Screws ISO 7379 (Steel)* → Page 1058
- *Stainless Steel Shoulder Screws ISO 7379* → Page 1059

How to order

1	d₁
2	d₂
3	l₁
4	Material

GN 732.1-M8-10-12-ST