


Application example



1	2	3									
d_1	d_2	d_3 Pin -0.02 Bore G7	d_4	d_5	l_1	l_2	l_3	l_4 min.	A/F	Spring load in N \approx	
										Initial	End
34	M 10 x 1	5	8,6	15,5	45	5	19	17	10	7	17
42	M 12 x 1,5	6	9,9	19	53	6	21	19	12	9	24
53	M 12 x 1,5	6	9,9	22,5	59	6	21	19	12	9	24
53	M 16 x 1,5	8	13,9	22,5	68	8	28	26	16	11	30

Specification

- Knurled knob 7336
Plastic (Polyamide PA)
Black, matte finish
- Cover cap
Plastic (Polyamide PA)
Light gray, matte finish
- Fixing thread steel
Zinc plated, blue passivated
- Plunger pin
Stainless steel AISI 303
- Load Rating Information → Page 2132
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Clamping knobs with indexing plunger GN 7336.7 are used for positioning, securing and clamping adjusting elements at the same time.

The axial movement of the handle (pulling) pulls the plunger pin from the engaged position against the spring force, with the star knob at the same time remaining connected with form-lock to the clamping screw via a hexagonal element, allowing both clamping and releasing.

see also...

- List of Indexing Plunger Types → Page 884 ff.
- Knurled Knobs GN 7336 → Page 626

How to order	1	d_1
	2	d_2
	3	d_3
GN 7336.7-42-M12x1,5-6		