



d <sub>1</sub>	d <sub>2</sub>	s	for threaded bolts
6,4	17	3	M 6
8,4	23	4	M 8
10,5	28	4	M 10
13	35	5	M 12
15	40	5	M 14
17	45	6	M 16
21	50	6	M 20
25	60	8	M 24
31	68	10	M 30

**Specification**

- Heat-treated steel
  - tempered hardness (350 + 80) HV 30
  - phosphate-treated
  - blanked
  - not deburred

- RoHS

**Information**

Washers DIN 6340 are mainly used for elongated holes.

see also...

- Heavy duty washers GN 6339 → Page 812

How to order

**DIN 6340-17**

1 d<sub>1</sub>