



**3 Type**

- E With threaded blind bore
- C With plain blind bore H9
- B With plain through bore H7

d <sub>1</sub>	d <sub>2</sub> Type E			d <sub>3</sub> H9 Type C	d <sub>4</sub> H7 Type B	d <sub>5</sub>	d <sub>6</sub>	d <sub>7</sub>	h <sub>1</sub>	h <sub>2</sub>	Length l	t <sub>1</sub> min.	t <sub>2</sub> min.
45	M 6	M 8	-	B 8	-	-	-	21	26	10	-	12	14
56	M 8	M 10	M 12	B 8	B 10	22	23	26,5	29	11	22	13	14
70	M 10	M 12	M 16	B 10	B 12	26	28	32,5	35	13	27	17	21

**Specification**

- Plastic Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 130 °C
  - Black-gray, similar to RAL 7021, matte

• Star knob upper part (matte finish):

- Black-gray, RAL 7021 ● DSG
- Orange, RAL 2004 ● DOR
- Gray, RAL 7035 ● DGR
- Yellow, RAL 1021 ● DGB
- Blue, RAL 5024 ● DBL
- Red, RAL 3000 ● DRT
- Green, RAL 6017 ● DGN

- Star knob upper part and lower part ultrasonically welded

- Bushing
  - Type B / C: Steel, blackened
  - Type E: Brass

- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158

• RoHS

**Information**

The design of the star knobs GN 636 matches the product family Ergostyle®.

see also...

- Product Family Ergostyle® → Page 18

How to order

1	d <sub>1</sub>
2	d <sub>2</sub> (d <sub>3</sub> , d <sub>4</sub> )
3	Type
4	Color upper part

**GN 636-56-M10-E-DSG**