



ELESA Original design TSD. / TSR.



d ₁ GN 740				d ₁ GN 740.2	d ₂	l ₁	l ₂	l ₃	s ₁	s ₂	e ≈
G 1/8	M 10 x 1,5	M 12 x 1,5	-	-	15	9	15	-	19	-	22
G 1/4	M 14 x 1,5	-	-	G 1/4	15	9	15	17	19	19	22
G 3/8	M 16 x 1,5	-	-	G 3/8	17	9	15	18	22	22	25,5
G 1/2	M 18 x 1,5	M 20 x 1,5	-	G 1/2	20,5	11	18	20	26	27	32
G 3/4	M 22 x 1,5	M 25 x 1,5	M 26 x 1,5	G 3/4	25	12	20	22	32	32	37
G 1	M 35 x 1,5	-	-	G 1	31	13	22	23	38	38	44
G 1 1/4	M 40 x 1,5	-	-	G 1 1/4	38	14	24	26	46	46	53,5
G 1 1/2	-	-	-	G 1 1/2	46	15	26	28	55	55	63,5

Specification

- Plastic Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - red
 - temperature resistant up to 100 °C
- Sealing ring rubber NBR (Perbunan)
- O-ring rubber NBR (Perbunan)
- *Elastomer characteristics* → Page 1483
- *Plastic characteristics* → Page 1483
- **RoHS compliant**

Information

Threaded plugs GN 740 / GN 740.2 are generally supplied as drain plugs in red color.

see also...

- *Threaded plugs GN 745 (without symbol)* → Page 1111
- *Threaded plugs GN 741 / GN 742 (Aluminum)* → Page 1114

How to order (with overlying sealing)

GN 740-G^{3/4}

1 d₁

How to order (with collared O-ring)

GN 740.2-G^{1/2}

1 d₁