


GN 745.2



ELESA Original design TN.

**2 Coding**

- 1 without vent hole
- 2 with vent hole




d <sub>1</sub>				GN 745.2		d <sub>2</sub> Vent hole	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	s	e ≈
GN 745											
G 1/8	M 10 x 1,5	M 12 x 1,5	-	-	2	15	9	16	19	22	
G 1/4	M 14 x 1,5	-	-	G 1/4	2	15	9	17	19	22	
G 3/8	M 16 x 1,5	-	-	G 3/8	2	17,5	9	18	22	25,5	
G 1/2	M 18 x 1,5	M 20 x 1,5	-	G 1/2	2	21	11	20	27	32	
G 3/4	M 22 x 1,5	M 25 x 1,5	M 26 x 1,5	G 3/4	2	25	12	22	32	37	
G 1	M 35 x 1,5	-	-	G 1	2	31	13	23	38	44	
G 1 1/4	M 40 x 1,5	-	-	G 1 1/4	2	38	14	26	46	53,5	
G 1 1/2	-	-	-	G 1 1/2	2	46	15	28	55	63,5	

**Specification**

- Plastic (Polyamide PA)
  - glass fiber reinforced
  - black, matte
  - temperature resistant up to 100 °C
- Sealing ring / O-ring  
Rubber NBR (Perbunan)
- *Elastomer characteristics* → Page 1483
- *Plastic characteristics* → Page 1483
- RoHS

**Accessory**



**Information**

Suitable for threaded plugs GN 745 are self adhesive, matte anodized Aluminum discs with graphic symbols (0.3 mm thick) which can be supplied.

see also...

- *Plugs GN 741 / GN 742 (Aluminum)* → Page 1114

How to order (with flat sealing ring)	1	d <sub>1</sub>
GN 745-G <sup>3</sup> / <sub>4</sub> -1	2	Coding

How to order (with O-ring)	1	d <sub>1</sub>
GN 745.2-G <sup>1</sup> / <sub>2</sub> -1	2	Coding

How to order (Aluminum disc)	3	d <sub>3</sub>
GN 740.1-25		

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9