



d_1	d_2	e	l_1	l_2	s	Recommended tightening torque in Nm
G 3/8	17	25	9	16	22	8 ... 10
G 1/2	20,5	29,5	11	18	26	8 ... 10
G 3/4	25	36,5	12	20	32	8 ... 10

Specification



- Plastic (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 80 °C
 - Yellow, RAL 1021, matte finish ● **GB**
- Seal
 - Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

Information

ATEX Threaded plugs GN 745.6 are suitable for use in an explosion risk environment. They comply with the European explosion protection guidelines (ATEX) 2014/34/EU.

A detailed operating instruction is available and included with every threaded plug.

see also...

- *Threaded Plugs GN 741 / GN 742* → Page 1590

How to order

GN 745.6-G¹½-G²B

1 d_1

2 Color

