



d ₁	l ₁ ±0,5	b	d ₂	h	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇ max.
30	200	18	M 8	60	230	170	265	85	17	8,5
30	250	18	M 8	60	280	220	315	85	17	8,5
30	300	18	M 8	60	330	270	365	85	17	8,5
30	400	18	M 8	60	430	370	465	85	17	8,5
30	500	18	M 8	60	530	470	565	85	17	8,5
30	600	18	M 8	60	630	570	665	85	17	8,5

Specification

Handle tube

Wall thickness 1,5 mm

• Aluminum

- Powder coated
Black, RAL 9005, textured finish ● **SW**

- Anodized, natural color ● **EL**

- Anodized, natural color ● **ELG**

Handle legs / Covers, light gray, matte finish

• Stainless steel AISI 304

- Ground, matte shiny finish ● **NG**

Handle legs / Covers, black, matte finish

Handle legs

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature up to 100 °C
- Threaded bushing steel, zinc plated

Covers

Plastic, thermoplastic elastomer (TPE)

Fastening set

- Socket cap screws ISO 4762
Steel, zinc plated
- Black passivated for SW / EL / NG
- Blue passivated for ELG
- Hex nuts ISO 4032-M8
Steel, zinc plated, blue passivated
- Washers DIN 125
Steel, zinc plated, blue passivated

RoHS

Owing to their large range of variants and their classic design, GN 666.1 tubular handles are the perfect choice for many applications.

The mounting screws included, allow the installation from the back or the operator's side. Tubular handles GN 666.1 and GN 666 of identical length are also suitable for double mounting, e.g. for sliding doors.

see also...	Page
GN 666 Tubular Handles (Mounting from the Back)	QVX
GN 666.7 Tubular Handles (Mounting from the Operator's Side)	QVX

Technical Information

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Tube aluminum)

1	d ₁
2	l ₁
3	Material / Finish

GN 666.1-30-600-SW

How to order (Tube stainless steel)

1	d ₁
2	l ₁
3	Material / Finish

GN 666.1-30-400-NG