



ELESA Original design EKH.



iF product design award

Length l	¹ d ₁ H7 Bore	² s H9 Square	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆ ≈	Ø Handle
100	B 12	V 12	24	23,5	30	33	52,5	10	17	16	65	22
125	B 14	V 14	28	26,5	35	40	62	14	18	18,5	80	24

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 80 °C
- black-gray, matte
similar to RAL 7021
- Hub bushing
Steel, blackened
- Threaded bushing to accept the revolving handle
Brass
- Revolving handles
- Plastic, Technopolymer
black, matte
- Spindle steel
zinc plated, blue passivated
- Color of the cover cap (matte):

● DSG
● DOR
● DGR
● DGB
● DBL
● DRT
- Square DIN 79 → Page 1424
- Cross hole GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- Plastic characteristics → Page 1483
- RoHS



Information

The design of the cranked handles GN 670 matches the product family Ergostyle®.

The protruding steel bushing ensures an accurate bore and square to bore face. It can be retained with a pin or a retaining screw. The link between the cranked handle and shaft can be established either with a keyway or a follower pin.

see also...

- Product family Ergostyle® → Page 17

How to order

GN670-100-B12-DOR

¹	Length l
²	d ₁ (s)
³	Color of the cap