



GN 798				$d_3$	$d_4$	$l_1$	$l_2$	$l_3 \approx$	$l_4$
$d_1$	$d_2$								
16	M 6	-	-	10	13	41,5	12	2,5	15
18	M 6	M 8	-	10	14,5	56	13	2,5	19
22	M 6	M 8	M 10	14	18,5	59	14	2,5	21
24	M 8	M 10	-	14	18,5	74	16	2,5	27
25	M 10	-	-	16	20	84	16	2,5	30

GN 798.1				$d_3$	$d_4$	$l_1$	$l_2$	$l_3 \approx$	$l_4$
$d_1$	$d_2$								
KT	NI								
16	-	M 6	-	10	13	41,5	12	2,5	15
18	18	M 6	M 8	10	14,5	56	13	2,5	19
22	22	M 8	M 10	14	18,5	59	14	2,5	21
24	24	M 8	M 10	14	18,5	74	16	2,5	27
25	-	M 10	-	16	20	84	16	2,5	30

**Specification**

**GN 798**

**Handle**

- Plastic Polyamide (PA)
- Operating temperature up to 90 °C
- Black, matte finish

- Aluminum
- Polished

**Spindle**

Steel  
Zinc plated, blue passivated

**GN 798.1**

**Handle**

- Plastic Polyamide (PA)
- Operating temperature up to 90 °C
- Black, matte finish

- Stainless steel AISI 303
- Fine turned, plain

**Spindle**

Stainless steel AISI 303

RoHS



KT

AL

KT

NI

The design of the revolving handles GN 798 / GN 798.1 is characterized by their shape, consisting of two cylinders. It gives the hand an excellent grip.

see also...

**GN 798.1** Revolving Handles (Spindle Stainless Steel) QVX

**GN 798.2** Revolving Handles (Spindle Steel, with Internal Thread) QVX

**GN 798.3** Retractable Handles

(Retractable Mechanism Steel, with Hold in Both Positions) QVX

**GN 798.7** Safety Retractable Handles (Automatic Return to the Retracted Position) QVX

**Technical Information**

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

How to order (Spindle Steel)

**GN 798-AL-24-M10**

1 Material

2  $d_1$

3  $d_2$

How to order (Spindle stainless steel)

**GN 798.1-NI-18-M6**

1 Material

2  $d_1$

3  $d_2$