



elesa
Original design EKH.



IF product design award

Length l	¹ d ₁ H7 Bore	² s H9 Square	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆ ≈	Ø Handle
100	B 12	V 12	24	23,5	30	33	52,5	10	17	16	65	22
125	B 14	V 14	28	26,5	35	40	62	14	18	18,5	80	24

Specification

Body

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature 0 °C to +90 °C
- Black-gray, matte finish, similar to RAL 7021

Cover cap

- Plastic, Polyamide (PA)
 - Black-gray, RAL 7021, matte finish
 - Orange, RAL 2004, matte finish
 - Gray, RAL 7035, matte finish
 - Yellow, RAL 1021, matte finish
 - Blue, RAL 5024, matte finish
 - Red, RAL 3000, matte finish
- **DSG**
 - **DOR**
 - **DGR**
 - **DGB**
 - **DBL**
 - **DRT**

Hub bushing

Steel, blackened

Threaded bushing

to accept the revolving handle
Brass

Revolving handle

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle steel
- Zinc plated, blue passivated

RoHS

The design of the cranked handles GN 670 matches the product family Ergostyle®.

The protruding steel bushing ensures an accurate bore and square to bore face. It can be retained with a pin or a retaining screw. The link between the cranked handle and shaft can be established either with a keyway or a follower pin.

Technical Information

Technical Information	Page
Product Family Ergostyle®	QVX
Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

Accessory

GN 184 Countersunk Washers (for Axial Fastening)	QVX
--	-----

How to order

GN 670-100-B12-DOR

¹	Length l
²	d ₁ (s)
³	Color of the cover cap