



1.1

1.2

1.3

1.4

2

d ₁	d ₂	d ₃	l ₁ ≈ (arrested)	l ₂	l ₃	l ₄	l ₅
22	M 6	20	82	22	5,5	73	13
24	M 6	20	97	22	5,5	88	13
25	M 6	20	107	22	5,5	98	13

2.1

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- temperature resistant up to 90 °C
- black, matte
- revolving

KT

- **GN 798.7**
Retractable mechanism
- Axle part
Steel 1.0718, blackened
- Flat base
Sintered Steel, blackened

- **GN 798.8**
Retractable mechanism
Stainless Steel
- Axle part AISI 303
- Flat base
Sintered Steel AISI 316 LHC

- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

Safety retractable handles GN 798.7 / GN 798.8 are suitable for applications such as cranked handles and handwheels if the handle may not be locked in the operating position.

In order to bring the handle into the operating position it has to be turned first through 90° to a stop against a torsion spring and then it is pushed against spring pressure into its hold position.

By maintaining the forward thrust on the handle, the handwheel can easily be rotated.

When releasing the handle, the springs return it back to the retracted position.

2.2

2.3

2.4

How to order (Retractable mechanism Steel)

GN 798.7-KT-24

1	Material
2	d ₁

How to order (Retractable mechanism St. Steel)

GN 798.8-KT-25

1	Material
2	d ₁

