



**4 Type**

- A** With two through holes
- B** With two countersunk holes for socket cap screws
- C** With two tapped holes

d <sub>1</sub>	d <sub>2</sub> H10 Recommended shaft tolerance h11		b ±0,2	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	m		s	x ≈ Max. protrusion of cap screw	Adjustable hand lever for d <sub>3</sub>
	Bore series 1	Bore series 2						Bore series 1	Bore series 2			
30	B 12	-	11	M 4	4,5	3,5	M 4	21	-	2,1	0,7	GN 311-30-M4-12-SW
32	B 14	-	11	M 4	4,5	3,5	M 4	23	-	2,1	0,7	GN 311-30-M4-12-SW
36	B 15	B 16	13	M 5	5,5	4,5	M 5	25,5	26	2,1	1,4	GN 311-30-M5-13-SW
42	B 18	B 20	15	M 5	5,5	4,5	M 5	30	31	3	0,6	GN 311-30-M5-15-SW
48	B 22	B 25	15	M 5	6,5	5,5	M 6	35	36,5	3	0	GN 311-45-M5-16-SW
55	B 28	B 30	15	M 6	6,5	5,5	M 6	41,5	42,5	3	0,5	GN 311-45-M6-18-SW
60	B 32	B 35	15	M 6	6,5	5,5	M 6	46	47,5	4	0,4	GN 311-45-M6-19-SW
65	B 40	-	15	M 6	6,5	5,5	M 6	52,5	-	4	0,5	GN 311-45-M6-20-SW

**Specification**

- Stainless steel **NI**
- Sintered steel AISI 316LHC
- Socket cap screw DIN 912  
Stainless steel AISI 304
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

**Accessory**

- Adjustable Hand Levers GN 311  
→ Page 1159
- Damping Washers GN 7062.30  
→ Page 1161

**Information**

With semi-split stainless steel shaft collars GN 7062.2, e.g., axles are attached to housing, or wheels and washers are installed on shafts.

They can be assembled safely and easily with a high clamping force by reducing the slot height, without damaging the surface of shafts and axles.

The thread d<sub>3</sub> for sizes d<sub>1</sub> = 30 to 36 is designed as a through hole; for sizes d<sub>1</sub> = 42 and larger, it is designed as blind hole.

see also...

- Split Stainless Steel Shaft Collars GN 7072.2 (with Flange Holes) → Page 1156
- Semi-Split Shaft Collars GN 706.2 → Page 1148

How to order	
1	d <sub>1</sub>
2	d <sub>2</sub>
3	Material
4	Type

**GN 7062.2-55-B28-NI-B**