



1

2

| d ₁ | Length l | | | | d ₂ | e | h | m |
|----------------|----------|----|----|-----|----------------|-----|----|------|
| M 5* | 37 | - | - | - | 14 | - | 10 | 4,7 |
| M 6 | 32 | 42 | 52 | - | 12 | 2,2 | 7 | 5,2 |
| M 8 | 38 | 48 | 63 | 83 | 16 | 3 | 9 | 6,8 |
| M 10 | 44 | 54 | 64 | 84 | 20 | 3,6 | 11 | 8,4 |
| M 12 | 55 | 65 | 85 | 105 | 25 | 4,5 | 13 | 10,8 |

* Clamping bolt M5: bolt end and thrust pad are not hardened and not removable.

Specification

- Screw DIN 6332 → Page 1065
Steel
 - Thrust point hardened (Type SK)
 - Blackened
- Thrust Pad DIN 6311 → Page 1066
Steel
Case-hardened
- Hexagon nuts ISO 4032 / DIN 934
Steel
Zinc plated, blue passivated
- RoHS

Information

By means of the retaining ring in the thrust pad a simple and toggle link between screw and thrust pad is created.

The two hexagon nuts are included parts of the order.

see also...

- *Holders for Clamping Screws GN 801*
(for Toggle Clamps with Forked Clamping Arm) → Page 815
- *Holders for Clamping Screws GN 809*
(for Toggle Clamps with Solid Clamping Arm) → Page 818

How to order

GN 802-M8-48

1 d₁

2 Length l