


**3 Type**

**A** Mounting with countersunk screw



**1**

**2**

| r  | d <sub>1</sub> | b  | d <sub>2</sub> | d <sub>3</sub> | l <sub>1</sub> | l <sub>2</sub> | l <sub>3</sub> | l <sub>4</sub> | Load F max. in N |
|----|----------------|----|----------------|----------------|----------------|----------------|----------------|----------------|------------------|
| 45 | M 6            | 13 | 19             | 9              | 12             | 13             | 8,5            | 0,5            | 500              |
| 65 | M 8            | 18 | 25             | 14             | 14             | 16             | 10,5           | 0,6            | 1000             |

**Specification**

- Latch  
Zinc die casting  
Powder coated  
Black, RAL 9005, textured finish  
Silver, RAL 9006, textured finish
- Indexing mechanism  
Stainless steel
- Countersunk screw DIN 7991  
Stainless steel
- RoHS

**4**

**Information**

Stop locks GN 720 may be used as stops and feature a high degree of stability.

The inside ball-spring latching mechanism has 4 latching positions at a distance of 90° each. Thanks to the bolt attachment using the countersunk screw, the latching position is freely selectable.

The bar is solid and may be machined, if required.

The countersunk screw is enclosed part of the order.

**How to order**

**GN 720-65-M8-A-SW**

- 1** r
- 2** d<sub>1</sub>
- 3** Type
- 4** Color

