



Detail Z; End of thread:

M4 / M5



M6 ... M12



2 Type

- ST** Steel, standard spring load
- NI** Stainless steel, standard spring load

1

d ₁	d ₂	d ₃	l ₁	l ₂	l ₃	w Compression	Spring load in N ≈	
							Initial	End
M 4	2,5	6	6,5	3	5	0,8	8	14
M 5	3	8	8,5	4	6,7	0,9	8	14
M 6	3,5	10	9	5	-	1	11	18
M 8	4,5	13	11	5,5	-	1,5	18	31
M 10	6	16	14	6	-	2	24	45
M 12	8	18	15	7	-	2,5	26	49

Specification

- Type ST
 - Housing
Steel, blackened
 - Ball
Steel, hardened
- Type NI
 - Housing
Stainless steel AISI 303
 - Ball
Stainless steel AISI 420C, hardened
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Spring plungers GN 815 are used as stops as well as thrust elements or ejectors.
The collar gives a defined installation position.

How to order

GN815-M8-ST

- 1** d₁
- 2** Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

