


- 2 Type**
- A** With thread, mounting from above
 - UA** With groove, mounting from above
 - UB** With groove, mounting from the front

Application examples



d ₁ Thread	d ₁ ^{+0.6 +0.4} Bore	h ₁			b h11	d ₂	h ₂	h ₃	h ₄	k	Length l	m						
		Type A	Type UA	Type UB														
M 6 x 1	6	5	10	20	10	15	25	10	15	20	10	4,5	6	5	1,6	5,6	35	22
M 8 x 1	8	8	15	20	12	20	30	15	20	30	12	5,5	8	6	2,6	6,6	40	25
M 10 x 1	10	10	20	30	15	20	30	20	25	35	15	6,5	10	7,5	3,6	8,6	45	30

Specification

- Aluminum **AM**
- Matte ground
- Reference line
Laser-engraved, black discharged
- ISO Fundamental Tolerances → Page 2151
- RoHS

Accessory

- Adjusting Screws GN 827 → Page 1930
- Knurled Nuts GN 827.1 → Page 1932

Information

Bearing blocks GN 828 are used in combination with adjusting screws GN 827 for simple adjustment and positioning tasks.

For processing and assembly equipment on which attachments and mechanisms must be regularly exchanged, particularly simple adjustments can be achieved by combining adjusting screws GN 827, knurled nuts GN 827.1 and bearing blocks GN 828 of the types UA and UB to ensure that settings are retained even between uses.

On the opposing part, type A or threading already present in the mounting plate can be used.

How to order		1	d ₁
		2	Type
		3	h ₁
		4	Material
GN 828-8-UA-20-AM			

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9