



Length l	d							a	b	h	t min.				
	Standard material (PP)	HT material (PA)									M4	M5	M6	M8	M10
86 ±0,5	M 5	M 6	-	-	-	M 6	-	14	23	44	-	10	12	-	-
94 ±0,5	M 5	M 6	-	-	-	-	-	14	24	48	-	10	12	-	-
117 ±0,5	M 4	M 5	M 6	M 8	M 6	M 8		15	25	49	10	10	12	13	-
120 ±0,5	M 5	M 6	M 8	-	-	-		15	25	49	-	10	12	13	-
132 ±0,5	M 5	M 6	M 8	-	-	-		16	26	54	-	10	12	13	-
150 ±1	M 6	M 8	M 10	-	-	-		16	27	56	-	-	12	13	17
160 ±1	M 6	M 8	M 10	-	-	-		16	27	55	-	-	12	13	17
179 ±1	M 8	M 10	-	-	M 8	-		16	27	57	-	-	-	13	17
235 ±1	M 8	M 10	-	-	-	-		18,5	29	61	-	-	-	13	17
300 ±1	M 10	-	-	-	-	-		22	32	64	-	-	-	-	17

Specification

- Plastic Technopolymer (Polypropylene PP)
 - Shock-resistant
 - Temperature resistant up to 100 °C
 - Black, matte finish

3

Information

Cabinet U-handles GN 725 have a very ergonomic elliptical profile.

see also...

- Cabinet U-Handles GN 565 (Aluminum) → Page 106
- Cabinet U-Handles GN 625 (Plastic) → Page 118
- Cabinet U-Handles GN 525 (Duroplast) → Page 119

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 200 °C
 - Black, matte finish

HT

- Threaded bushing Brass
- Strength Properties → Page 2116
- Plastic Characteristics → Page 2158
- RoHS

How to order (Resistant up to 100 °C)	1	Length l
GN 725-179-M8	2	d

How to order (Resistant up to 200 °C)	1	Length l
GN 725-86-M6-HT	2	d
	3	Material