



Size	F _H in N Holding capacity	b ₁	b ₂ +0,5	b ₃	b ₄ ≈	b ₅	b ₆ ≈	d ₁	d ₂	h ₁
55	550	23	15	11	25	22	16	2	3,2	12

Size	h ₂	l ₁ ≈	l ₂ -1	l ₃ ≈	m ₁	m ₂	m ₃	m ₄	r ≈
55	8	57	40	34,5	5,5	10	3,8	14	26

Specification

- Steel **ST**
- Zinc plated, blue passivated
- Stainless steel AISI 304 **NI**
- *Stainless Steel Characteristics* → Page 2166
- RoHS



Information

Toggle latches GN 832.4 are used for the secure holding of flaps, container lids, etc. They lock securely over the center and are thus vibration proof.

The components to be linked are held in position by the elasticity of the U-bolt latch.

The load specified in the table is simply a guideline value for the nominal static pulling force the latch can withstand. The holding capacity can be adversely affected by the conditions under which the toggle latch is used, such as vibration or shock loads.

The catch bracket is included.

How to order

GN 832.4-55-ST

1	Size
2	Material