



**3 Type**

- A With arrow
- B Neutral, without indicator point or scale
- S With scale 0...9, 20 graduations

**4 Identification no.**

- 1 With grub screw
- 2 With collet

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> H8 Bore		<b>2</b> d <sub>3</sub> Collet	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	d <sub>7</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	Length l	t
22	B 5	-	-	16	14	M 4	20	22	16	4,3	8	12,5	-
27	B 6	-	Z 6	20	18	M 4	25	26	20	4,3	9	14	14
34	B 6	B 8	Z 8	25	23	M 5	32	30	24	4,2	10	15	17
42	B 8	B 10	Z 10	32	30	M 5	40	34	28	4	11	16	20

**Specification**

**Knob**

- Aluminum
- Anodized, black
- Arrow for type A  
White, laser-engraved
- Scale for type S  
White, laser-engraved

**Cover**

Plastic, light gray

**Collet / Hex nut**

Brass

**Grub screw DIN 916**

Stainless steel  
with internal hex and serrated point

RoHS

**On request**

- Special graduations  
(see „How to Order Graduations“)

The light gray cover of the control knobs GN 726.1 shrouds the fixing components as well as the shaft end. The cover also lends itself for a logo or other symbols.

The collet version permits a simple adjustment of the types with scale or arrow.

Scale and arrow on the control knobs are indelibly marked and easily legible since the engraved „aluminum colored“ numbers contrast with the black anodized surface.

Besides the standard scale (type S) the control knobs can be supplied with any type of graduation.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to Order Graduations“.

see also...

	Page
GN 626 Control Knobs (Plastic)	QVX
GN 726.2 Control Knobs (Aluminium, with Scale Ring)	QVX

**Technical Information**

How to Order Graduations	QVX
ISO Fundamental Tolerances	QVX

**Accessory**

GN 826 Clamping Elements (for Adjustable Spindles)	QVX
--	-----

How to order

<b>1</b> d <sub>1</sub>	
<b>2</b> d <sub>2</sub> (d <sub>3</sub> )	
<b>3</b> Type	
<b>4</b> Identification no.	

**GN 726.1-42-B10-A-1**

