



2 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

1

l_1	GN 728	GN 728.5	b	d_1	d_2	d_3	h_1	h_2	l_2	l_3	s	t_1 min.	t_2
120	120	-	22,5	M 6	6,4	11	42,5	6,5	147	108	8	10	6,5
180	-	-	27	M 8	8,4	13,5	47,5	7,5	214	165	10	12	8,5

Specification

GN 728

Aluminum die casting

- Plastic coated
 - Black, RAL 9005, textured finish ● **SW**
 - Silver, RAL 9006, textured finish ● **SR**
- Plain finish, tumbled ○ **BL**

GN 728.5

Stainless steel precision casting AISI CF-8

Matt shot-blasted

RoHS

The installation of cabinet U-handles GN 728 / GN 728.5 can be carried out from the back (type A) as well as from the operator's side (type B).

see also...

	Page
GN 528 Cabinet U-Handles (Plastic, Mounting from the Operator's Side)	QVX
GN 528.1 Cabinet U-Handles (Plastic, Mounting from the Back)	QVX

Technical Information

	Page
Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order (Aluminum die casting)

GN 728-120-A-SW

1	l_1
2	Type
3	Finish

How to order (Stainless steel precision casting)

GN 728.5-120-B

1	l_1
2	Type