



1 2

d ₁	d ₂ H8	b	d ₃	d ₄	d ₅	l ₁	l ₂	t ₁ min.	t ₂ +0,2	s ^{+0,3 +0,1}
34	B 6 B 8	28	M 5	6	20	20	7,5	14	4	4
42	B 8 B 10	35	M 5	6	30	22	7,5	16	4	4

Specification

Knob

- Aluminum
- Anodized, black
- Indexing line
 - White
 - Laser-engraved

Grub screw DIN 916

Stainless steel
with internal hex and serrated point

RoHS

Control knobs GN 729 are usually selected for applications which require a limited movement within 180°.

With the aid of limiting pins which protrude into the circular groove the angle of rotation can be restricted. The bore d₄ is for a spring plunger GN 614 to act as a simple detent.

The indexing line is indelible and visible from two sides.

Technical Information

ISO Fundamental Tolerances

Page

QVX

Accessory

GN 826 Clamping Elements (for Adjustable Spindles)

QVX

How to order

GN 729-42-B8

1 d₁

2 d₂

