



3 Type

- E With threaded blind bore
- D With threaded through bore

d₁	d₂	d₃	d₄	b	h₁	h₂	t₁ min.	t₂
46	M 6	13	6,5	6	22,5	6	12	10
46	M 8	13	8,5	6	22,5	6	15	13
58	M 8	16	8,5	7	26,5	7	15	13
58	M 10	16	10,5	7	26,5	7	18	16

Specification

Stainless steel precision casting AISI CF-8

Matte shot-blasted finish

MT

RoHS

see also...

GN 432 Wing Nuts

GN 434 Wing Nuts

GN 5345 Lobed Knobs

DIN 6335 Hand Knobs

Page

QVX

QVX

QVX

QVX

Technical Information

Stainless Steel Characteristics

QVX

How to order

GN 834-46-M8-E-MT

1 d₁

2 d₂

3 Type

4 Finish

