



ROSTFREI
Inox
Stainless
Steel

2

3

d_1		Mesh size in μm		d_2	d_3	l_1	l_2	s
G 1/2	M 20 x 1,5	100	500	26	10	8,5	7,5	23
G 3/4	M 26 x 1,5	100	500	32	14	9	8	30
G 1	M 33 x 1,5	100	500	40	20	11	8,5	36

Specification

- Body
 - Aluminum **AL**
 - Stainless steel AISI 303 **NI**
- Strainer
Stainless steel mesh AISI 304
- Strainer bezel
Plastic (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
- Sealing / O-Ring
Rubber NBR (Perbunan®)
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Accessory

- Mounting Nuts GN 7430 → Page 1632

On request

- Body in brass **MS**
- Other mesh size
- Other material for the strainer

1

Information

Breather strainers GN 7403 are used in enclosure and device construction. Inserted into the wall of the enclosure, they ensure pressure equilibrium between the inside of the enclosure and the outside.

Any dirt and dust particles carried by the medium (usually gas) are prevented from exiting depending on the mesh size. This protects the insides of sensitive devices and machinery parts from dirt and pollution and also protects the environment from any exiting dust.

The outside diameter of the enclosure with the recessed hexagon matches the bolt mounting holes for DIN 3852 threaded pipe connectors.

The sealing ring is embedded in a radial and plane-sided recess which makes the seal captive and prevents it from being squeezed out during tightening.

Assembly instruction:

For mounting on walls of less than 4 mm thickness please use mounting nuts GN 7430.

How to order

GN 7403-AL-G¹/₂-G²/₄-500³

1	Material
2	d_1
3	Mesh size