



**3 Type**

- D** With internal thread
- E** With threaded stud

<b>1</b> $d_1$	<b>2</b> $d_2$ Type D	<b>2</b> $d_3$ Type E	$d_4$	$h$	Length $l$	$t$ min.
17	M 5	M 5	10	14	9	7
21	M 6	M 6	12	17	10	11
25	M 6	M 6	14	21	10	11
33	M 8	M 8	18	29	14	12

**Specification**

**Knob**

- Plastic, phenolic resin (PF)
- Operating temperature up to 110 °C
- Black, shiny finish

**Threaded bushing for type D**

Brass

**Threaded stud for type E**

Steel  
Zinc plated, blue passivated

RoHS

Mushroom shaped knobs GN 76 are used as switching and operating elements. They are preferably operated with two fingers by pulling or pushing in the axial direction.

The mushroom shaped knobs of phenolic resin have good resistance to chemical influences.

**see also...**

	<b>Page</b>
<b>GN 676</b> Knurled Knobs	QVX
<b>GN 676</b> Knurled Knob Screws	QVX

**Technical Information**

Plastic Characteristics	QVX
-------------------------	-----

**How to order**

**GN 76-25-M6-D**

<b>1</b>	$d_1$
<b>2</b>	$d_2$ ( $d_3$ )
<b>3</b>	Type

