



1

For power clamps GN 864 Size	s	d ₁	d ₂ ^{HB h6}	d ₃	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	m ₁	m ₂
20	32	M 5	7	5,5	7	9	76	5	10	15,5	2,1	22	17
32	42	M 6	9	6,5	9	11	109	6,5	12	20	2,1	30	25
40	52	M 8	11	8,5	11	13	131	7,5	14	23	2,1	37	30
50	62	M 10	13	10,5	13	16	162	9	16	27	3,1	44	47

Specification

- Aluminum
 - Anodized, black **ES**
 - Anti-stick coating
Polytetrafluorethylene (PTFE), green **FG**
- Socket cap screws DIN 912,
Centering guide bushings
Steel, blackened
- ISO Fundamental Tolerances → Page 2151
- RoHS

2 Information

Protective covers GN 864.1 are designed for power clamps GN 864 and protect the tensioning mechanism from penetrating dirt by covering the back side of the power clamp.

The type FG is equipped with an anti-stick coating of Polytetrafluorethylene (PTFE) for protection against welding spray and corrosion. Socket cap screws and centering guide bushings are included.

see also...

- Power Clamps GN 864 → Page 822

How to order	
1	s
2	Finish

GN 864.1-52-FG

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

