



1

$d_0$ Swivel ball joint $\varnothing$ GN 784	$d_1$	$d_2$	$d_3$	$d_4$	$d_5$	$h_1$	$h_2$	$m$	$s$
23	42	32,5	4,5	M 5	2	6	8,5	7	2,5
31	49	40	4,5	M 6	3	6	10,5	9	3
39	60	50	5,5	M 8	4	10	14,6	12	4
49	70	60	5,5	M 8	4	10	14,6	16	4

**Specification**

2

- Stainless steel AISI 304  
Matte, tumbled finish **MT**
- Countersunk screw DIN 7991  
Stainless steel AISI 304
- Half length tapered groove pin DIN 8745  
Stainless steel AISI 304
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Flanges GN 784.1 are mounted from below onto the GN 784 swivel ball joints. A half length tapered groove pin prevents any rotation.

The flange enables the swivel ball joint to be mounted on the upper surface. The  $d_2$  section with the three  $d_3$  drill holes is configured so that standard screws with washers can be used.

The half length tapered groove pin is mounted on the flange. The countersunk screw is included separately.

see also...

- *Swivel Ball Joints GN 784* → Page 1820

How to order

**GN 784.1-70-MT**

1  $d_1$

2 Finish